

# LEAVING YESTERDAY'S STANDARDS BEHIND THE EVOLUTION OF CLEAN.

Prevent microbial contamination with the cleanest fluid transfer solution available. Wilden's proven hygienic equipment meets all of the stringent requirements of the European Hygienic Equipment Design Group (EHEDG). Wilden's Hygienic pumps are 316L stainless steel and are ideally suited for applications where the highest degree of hygienic product transfer is required. Wilden's EHEDG certified products ensure superior containment and the prevention of microbial contamination of pharmaceutical and food products. Transfer your products with confidence, Wilden's EHEDG certified pumps - the evolution of clean.

- EHEDG compliant Doc. 2 & Doc. 8
- 316L stainless steel polished to 0.4  $\mu\text{m}$  (15  $\mu\text{-in}$ )
- 25 mm (1") to 76 mm (3")
- Tri-Clamp® style connections
- Union & Bolted Liquid paths
- Superior product containment
- Standard EN10204/3.1.B material certifications
- PTFE (FDA and USP Class VI) EPDM integral piston diaphragm option
- CIP (Clean in Place)
- SIP (Steam/Sterilize in Place)



**WILDEN**®  
A DOVER COMPANY

22069 Van Buren St. • Grand Terrace, CA 92313-5651 • Tel 909-422-1730 • Fax 909-783-3440 • [www.wildenpump.com](http://www.wildenpump.com)


Jansen Pompentechniek T: +31(0)485-371318 E: [info@pompentechniek.nl](mailto:info@pompentechniek.nl)

# Jansen

Hoogeindsestraat 5  
NL - 5447 PD Rijkevoort  
Nederland  
T : +31 (0) 485 - 371318  
F : +31 (0) 485 - 371918  
[info@pompentechniek.nl](mailto:info@pompentechniek.nl)  
[www.pompentechniek.nl](http://www.pompentechniek.nl)

POMPEN - & WATERTECHNIEK





## DIFFICULT APPLICATIONS

- Health & personal care products
- Pharmaceutical products
- CIP fluid & joint CIP product use
- Chromatography, separation, purification & filter feed
- Acids, solvents, caustics & alcohols



### **PV4 SANIFLO™ HYGIENIC PUMP**

- Lube-free operation
- Pro-Flo V™ air distribution system
- 38 mm (1-1/2") to 76 mm (3") Tri-clamp™ style connections
- Ball & mushroom check valves available
- Maximum solids passage 76.2 mm (3")
- Maximum flow rate 869 lpm (229 gpm)
- Maximum operating pressure 8.6 bar (125 psig)
- EHEDG certified to doc. 2 & doc. 8
- 3A certified to standard 44-03



### **UB2 UNITEC™ PUMP**

- Lube-free operation
- Uni-Flo™ air distribution system
- Drain pump contents without disassembly
- 25 mm (1") Tri-clamp™ style connections
- Superior product containment
- Maximum solids passage 3.0 mm (1/8")
- Maximum flow rate 58 lpm (15.4 gpm)
- Maximum operating pressure 7.0 bar (100 psig)
- EHEDG certified to doc. 2 & doc. 8

**WILDEN**®  
A DOVER COMPANY

22069 Van Buren Street, Grand Terrace, CA 92313-5607  
Telephone 909-422-1730 • Fax 909-783-3440  
wilden@wildenpump.com

Your Distributor:

**Jansen**  
POMPEN- & WATERTECHNIEK

Hoogeindsestraat 5  
NL - 5447 PD Rijkevoort  
Nederland  
T : +31 (0) 485 - 371318  
F : +31 (0) 485 - 371918  
info@pompechniek.nl  
www.pompechniek.nl

Printed in the U.S.A.

Copyright 2006 Wilden Pump & Engineering, LLC

WIL-14150-F-04

Jansen Pompechniek T: +31(0)485-371318 E: info@pompechniek.nl